


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		V		REVISED PER 063B-0095-05	4/1/05	SS	GS
		V1		REVISED PER ECO-09-020935	09SEP09	KK	AEG



- 1 PHENOLIC, BLACK.
- 2 DIALYL PHTHALATE, BLUE.
- 3 EACH POST WILL ACCEPT (SEE TABLE) TERMINATIONS OF #24 AWG MAX WIRE.
- 4 0.76µm[.000030] MIN GOLD ON MATING END FOR A LENGTH OF 5.08[.200] MIN. GOLD FLASH ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL.
- 5 2.54µm [.000100] MIN TIN-LEAD OVER 2.54µm [.000100] MIN NICKEL.
- 6 POSTS ARE SEMI-AUTOMATICALLY WIRABLE.
- 7 5.54[.218] IS REQUIRED WHEN JACKSCREWS ARE USED.
- 8 2.54µm [.000100] MIN TIN OVER 2.54µm [.000100] MIN NICKEL.
- 9 2.54µm [.000100] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

10	OBSOLETE	8	9	1	1	6.63 [.261]	6-205505-4
10	OBSOLETE	8	4	1	1	6.63 [.261]	6-205505-3
		8	4	1	3	16.74 [.659]	6-205505-2
	OBSOLETE	5	4	2	3	16.74 [.659]	4-205505-6
10	OBSOLETE	5	5	1	1	6.63 [.261]	3-205505-3
10	OBSOLETE	5	4	1	1	6.63 [.261]	3-205505-1
		5	4	1	3	16.74 [.659]	205505-1
	POST FINISH	CONTACT FINISH	HOUSING	NO OF TERM	A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN 13 OCT 97	Tyco Electronics Corporation Tyco Electronics Harrisburg, Pa 17105-3608				
DIMENSIONS: mm [INCHES]		CHK R. STONE 30 SEP 97	NAME G. STEINHÄUER				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC			
MATERIAL SEE CALLOUT		FINISH SEE CALLOUT		WEIGHT -		SIZE A1 CAGE CODE 00779 DRAWING NO 205505	
				CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 2:1		SHEET 1 OF 1	
						REV V1	