



NOTES:

MATERIAL:

HOUSING: DIALYL PHTHALATE, UL94V-0  
CONTACT MATERIAL: COPPER ALLOY  
CONTACT PLATING: GOLD PLATING OVER NICKEL  
INSERTION FORCE: 6 TO 16 OZ (0.56 TO 4.45N) PER CONTACT  
WITHDRAWAL FORCE: 6 TO 16 OZ (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: 10A PER CONTACT  
CONTACT RESISTANCE: 10mΩ MAX.  
INSULATOR RESISTANCE: 5000MΩ min.  
DIELECTRIC  
WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE:  
000 - No Contacts Assembled

<b>415 &amp; 438 SERIES CARD EDGE</b>	SW REFERENCE NO.: 415 ASSEMBLY	
	DRAWN: W.T	DATE: AUG. 01/2018
CHECKED:		DATE:
SCALE: 1:1	SHEET 1 OF 1	
DRAWING NUMBER: 415-041-000-212	ISSUE	1
PART NUMBER: 415-041-000-212		1



THIS SERIES FULLY CONFORMS TO  
THE EUROPEAN UNION DIRECTIVES  
2011/65/EU FOR RoHS COMPLIANCE.



EDAC INC  
TORONTO, ONTARIO  
CANADA

THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF EDAC INC., AND  
SHALL NOT BE REPRODUCED, OR COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.