



Actuator

704.335.0



<https://eao.com/p/704.335.0>

Your product:



704.335.0 Actuator

FRONT

Front bezel colour:	Grey
Front bezel material:	Plastic
Front dimension:	30 mm x 30 mm

MOUNTING

Design:	raised
---------	--------

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching action:	Momentary - Rest (a) - Momentary
Switching angle:	42° left / 42° right
Weight:	0.07 kg
Switching positions:	3 positions
Mechanical lifetime:	≤50 000 cycles of operation

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	- 40 °C ... + 55 °C
Storage temperature:	- 40 °C ... + 85 °C

OTHER

max. number of switching elements:

3


Short Description:

Actuator, 30 mm x 30 mm, Grey, Plastic, Momentary - Rest (a) - Momentary

Hints:


The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on

Dimension drawings:



A = Screw terminal

Mounting cut-outs:




A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm

Switching positions:



Wiring diagrams:

