

Actuator

704.012.418



<https://eao.com/p/704.012.418>

Your product:



704.012.418 Actuator

FRONT

Front bezel colour:	Nature
Front bezel material:	Aluminium
Front form:	round
Front dimension:	Ø 35 mm

MOUNTING

Mounting cut-out:	Ø 30.5 mm
Design:	flush

OPERATING-/INDICATION PART

Lens shape:	flush
Lens colour:	Yellow
Lens material:	Plastic
Lens optics:	transparent
Lens illumination:	non illuminative

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

MECHANICAL CHARACTERISTIC

Weight:	0.051 kg
Operating Travel:	ca. 5.8 mm ± 0.2 mm

Mechanical lifetime: ≤3 Mio. cycles of operation

Switching action: Momentary

Operating force: 8 N

AMBIENT CONDITION

Storage temperature: - 40 °C ... + 85 °C

IP Protection: IP65 front side

Operating temperature: - 40 °C ... + 55 °C

OTHER

Housing material: Plastic


max. number of switching elements: 3

Housing colour: Grey

Short Description: Actuator, Ø 30.5 mm, Ø 35 mm, flush, non illuminative, Yellow, Plastic, transparent, round, Nature, Aluminium, anodised, Momentary


Hints: Max. 3 switching elements can be clipped on, The colour of anodised aluminium parts can vary due to technical production reasons

Dimension drawings:




A = Screw terminal

Wiring diagrams:



Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm