



Technical specification:


Rated voltage:	4pos	5pos
IEC 61076-2-101	250 V	60 V
Current rating:	4 A at 40°C	
IEC 61076-2-101		
Insulation resistance:	>=100 MΩ	
IEC 60512		
Pollution degree:	3/2	
IEC 60664-1		
Degree of protection:	IP 67, in mated condition	
IEC 60529		
Temperature range:	-30°C ... +85°C	
EN 60512-11-10	-40°C	
EN 60512-11-4	-40°C ... +85°C	
Mating cycles:	>=100	
IEC 60512-9a		

Materials:

Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	PA GF, UL 94 V-0
Sealing:	FPM
Socket housing:	CuZn, nickel plated
Shroud:	spring steel, nickel plated

Installation specification:

recommended torque:	0,8-1 Nm
Conec installation tool:	Torque wrench: 36-000200
	Insert across flats 14: 36-000370
	Insert across flats 15: 36-000320



Part no:	Description:	Pos	Note:
43-01174	SAL - 12 - FSH4 - X10	4	
43-01175	SAL - 12S - FSH4 - X10	4	with shroud
43-01176	SAL - 12 - FSH5.1 - X10	5	
43-01177	SAL - 12S - FSH5.1 - X10	5	with shroud


DO NOT ALTER CAD DRAWING BY HAND

RoHS & REACH compliant

Index: b 21.08.13 MG Ä4884
Data sheet revised, width across flats of the counter nut changed, installation specification added

general tolerance: 0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm
± 1,5°

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH



dim. in mm

	date	name
drawn	11.10.07	Fromm
appd.	18.10.07	W.Schmidt

CONEC®

title:

Male socket M12x1 axial, backmounting, dip solder, X10

dwg no:

43K1A500

part no: