









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECO-13-004307	08MAR2013	DD	MB
A2		REVISED PER ECO-16-017603	06DEC2016	DD	AH





- NOTES:**
- 1 CODING 1- -1 AS SHOWN
 - 2 MOULD CAVITY MARKING
 - 3 SUPPLIER MARK
 - 4 MATERIAL IDENTIFICATION
 - 5 DATE CLOCK
 - 6 CAVITIES SUITABLE FOR TE MQS SOCKET HOUSING PN 968562
 - 7 FOR COUNTERPART INTERFACE DRAWING SEE SHEET 2 OF 2
 - 8 THROUGH HOLE NOT RELEVANT FOR FUNCTION OF CONNECTOR, TOOL RETENTION
 - 9 PRESSURE SENSOR NOT RELEVANT FOR FUNCTION OF CONNECTOR



2:1




COVER, 10POS.	0.00119	Z	9-2177198-1	1	PBT-GF15	WATER BLUE SIMILAR RAL 5021
COVER, 10POS.	0.00121	E	5-2177198-1	1	PBT-GF15	GREEN SIMILAR RAL 6017
COVER, 10POS.	0.00122	D	4-2177198-1	1	PBT-GF15	VIOLET SIMILAR RAL 4004
COVER, 10POS.	0.00121	C	3-2177198-1	1	PBT-GF15	BLUE SIMILAR RAL 5012
COVER, 10POS.	0.00121	B	2-2177198-1	1	PBT-GF15	NATURE
COVER, 10POS.	0.00121	A	1-2177198-2	1	PBT-GF15	CURRY SIMILAR RAL 1027
COVER, 10POS.	0.00121	A	1-2177198-1	1	PBT-GF15	BLACK RAL 9011
DESCRIPTION	MASS [kg]	COD	TE ORDER NO.	REV.	MATERIAL	SURFACE/COLOUR




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. POLIZZI CHK M. BANAS APVD M. BANAS	05MAY2011 05FEB2013 14FEB2013	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ± 0.15 1 PLC ± 0.10 2 PLC ± 0.10 3 PLC ± 0.10 4 PLC ± 0.10 ANGLES $\pm 2^\circ$		108-20319 APPLICATION SPEC	
MATERIAL SEE TABLE		WEIGHT SEE TABLE		SIZE A1	
-		CUSTOMER DRAWING		CAGE CODE 00779	
-		-		DRAWING NO. C=2177198	
-		-		RESTRICTED TO -	
-		-		SCALE 5:1	
-		-		SHEET 1 OF 2	
-		-		REV A2	

CODINGS
3:1



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

- NOTES:
- CODING A AS SHOWN
 - REFERENCES A, B, FOR CENTERLINE DEFINITION
1 mm ABOVE REFERENCE C
 - ALL SYMMETRIC DIMENSIONS ≡ 0.05 ⌀ ⊥
 - NO SPECIFIED RADII R0.5 mm
 - CAVITY MARKING, CHARACTERS DEEP
 - NO SPECIFIED WALL THICKNESS MIN. 1 mm
 - IN THIS AREA MAX. 0.03 mm BURRS PERMITTED
 - SPECIFICATION OF CONTACT PIN No 114-18063
 - HEADER MATERIAL: PBT-GF10
 - COUNTERPART SUITABLE FOR 10 POSITIONS MQS SOCKET HOUSING TE PN 2177198
 - CODING AREA WITHOUT CHAMFER



3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. POLIZZI CHK M. BANAS APVD M. BANAS	05MAY2011 05FEB2013 14FEB2013	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0x ⊕ ⌀ 0.1 A B		0 PLC ±0.15 1 PLC ±0.10 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.10 ANGLES ±2°		PRODUCT SPEC	
MATERIAL		SEE TABLE		APPLICATION SPEC	
8 9		SEE TABLE		108-20319	
CUSTOMER DRAWING		WEIGHT		SIZE CAGE CODE DRAWING NO	
SCALE 5:1		SHEET 2 OF 2		RESTRICTED TO	
REV A2		A1 00779		C=2177198	