


Solid shell, flat-wire bundle top cable entry - 507-198



feature saddle bar cable clamps for easy installation.

Backshell: Aluminum alloy
Hardware: CRES / passivated

Technical drawing of the 687-152-01F Floating Jackscrew, showing three views: front view, side view, and end view. Dimensions are provided in inches and millimeters.

Front View Dimensions:


- Overall width: .100 (2.54)
- W/SADDLES CLOSED
- Overall height: .031 (0.79)
- SILICONE PAD (2 PLACES)
- Distance between saddle centers: F

Side View Dimensions:

- Overall length: 1.22 (30.99)
- Distance from front face to saddle center: .89 (22.61)
- Overall height: A
- Distance from bottom face to saddle center: B
- 4-40 FLAT HEAD SCREW, 3/8" LONG.
- D THREAD

End View Dimensions:

- Overall width: E
- CLEARANCE HOLE
- Overall height: C



FEMALE JACKPOST
D THREAD - TYP
SYMBOL F

