

Han C M crimp contact 1.5 mm² Au/HMC



Image is for illustration purposes only. Please refer to product description.

Part number	09 32 200 6114
Specification	Han C M crimp contact 1.5 mm ² Au/HMC
HARTING eCatalogue	https://b2b.harting.com/09322006114

Identification

Category	Contacts
Series	Han [®] C HMC
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	1.5 mm ²
Conductor cross-section	AWG 16
Rated current	≤40 A
Contact resistance	≤1 mΩ
Stripping length	9.5 mm
Mating cycles with other HMC components	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	25
Net weight	3 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140187870
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors