





LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D7	ADD NEW PART -24	20 JAN 2015	AY	SZ



- 1 "AMP", PART NUMBER AND DATE CODE TO BE MARKED IN AREA SHOWN PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES;
- 2 HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING:
NOBLE METAL PLATING ON FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS.
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 6 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES
- 7 PCB - 0.0453 ±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn
OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE
- 8 THIS DIMENSION PLEASE REFER TO TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S.ZHAO	18JUN2008	TE Connectivity		
		CHK	S.ZHAO	18JUN2008			
		APVD	S.ZHAO	18JUN2008	NAME		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC		
INCHES					108-2292		
					APPLICATION SPEC		
					114-13251		
					WEIGHT		
					CUSTOMER DRAWING		
					SCALE		
					SHEET		
					REV		

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

D7


D5

.300	2.240	1.890	2.050	1.450	.195	5ACP + 8S	2-6450862-4
.250	3.240	2.890	3.050	1.925	.170	8P + 32S	2-6450862-3
.250	3.240	2.890	3.050	1.925	.170	8P + 32S	2-6450862-2
.115	.945	.595	.755	.2725	.1025	2LP + 8S	2-6450862-1
.200	3.265	2.915	3.075	2.175	.145	11HDP + 24S	1-6450862-8
	3.740	3.390	3.550	2.625	.170	3ACP + 8P + 24S	1-6450862-7
.250	2.415	2.065	2.225	1.425	.145	6P + 20S	1-6450862-6
.200	3.265	2.915	3.075	1.975	.145	10HDP + 32S	1-6450862-5
	2.420	2.070	2.230	1.330	.145	5P + 2LP + 24S	1-6450862-4
.250	3.790	3.440	3.600	2.900	.145	12P + 16S	6450862-6
	2.915	2.565	2.725	2.045	.170	6P + 2HDP + 20S	6450862-5
.115	.970	.620	.780	.2725	.1275	2LP + 8S	6450862-4
.200	3.065	2.715	2.875	1.975	.145	10HDP + 24S	6450862-3
.250	2.595	2.215	2.375	1.425	.170	6P + 24S	6450862-1
DIM S	DIM L	DIM U	DIM D	DIM W	DIM K	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES



MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.1

1 PLC ±.02

2 PLC ±.005

3 PLC ±.0020

ANGLES ±2°

FINISH

-

DWN S.ZHAO 18JUN2008

CHK S.ZHAO 18JUN2008

APVD S.ZHAO 18JUN2008

PRODUCT SPEC 108-2292

APPLICATION SPEC 114-13251

WEIGHT

-

CUSTOMER DRAWING

NAME

TE Connectivity

VERTICAL RECEPTACLE W/ P+S MULTI-BEAM XLE

SIZE A1

CAGE CODE 00779

DRAWING NO 6450862

RESTRICTED TO

-

SCALE 2:1

SHEET 2



OF 9

REV D7

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS		SIGNAL						POWER						
			6	5	4	3	2	1	P6	P5	P4	P3	P2	P1	
6450862-1	D C B A		AP	AP	AP	AP	AP	AP							
			AP	AP	AP	AP	AP	AP							
			AP	AP	AP	AP	AP	AP							
			AP	AP	AP	AP	AP	AP							
6P + 24S															


PART NUMBER	ROWS		SIGNAL							POWER																												
			6	5	4	3	2	1	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1																				
6450862-3	D C B A		AP	AP	AP	AP	AP	AP	AP																													
			AP	AP	AP	AP	AP	AP	AP															AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	
			AP	AP	AP	AP	AP	AP	AP															AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP
			AP	AP	AP	AP	AP	AP	AP															AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP
10HDP + 24S																																						



MFBL POWER CONTACT	GP
HOLD DOWN	HD
STD POWER CONTACT	GS
STD LP LOWER POWER CON.	LSI
SIGNAL CONTACT	AP
DESCRIPTION	CODE


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	S. ZHAO	18JUN2008	 TE Connectivity							
				CHK	S. ZHAO	18JUN2008								
				APVD	S. ZHAO	18JUN2008								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME								
INCHES				108-2292										
				APPLICATION SPEC										
				114-13251		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO				
				WEIGHT										
				CUSTOMER DRAWING										
MATERIAL		FINISH		SCALE		2:1		SHEET	3	OF	9	REV	D	
-		-		A1		100779		C=6450862		-				

PART NUMBER	ROWS		SIGNAL					POWER								
			5	4	3	2	1	P8	P7	P6	P5	P4	P3	P2	P1	
6450862-5	D C B A		AP	AP	AP	AP	AP									
			AP	AP	AP	AP	AP									
			AP	AP	AP	AP	AP									
			AP	AP	AP	AP	AP									
HD			HD													
6P + 2HDP + 20S																





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S_ZHAO 18JUN2008		 TE Connectivity	
DIMENSIONS: INCHES		CHN S_ZHAO 18JUN2008			
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±.1 2 PLC ±.02 3 PLC ±.005 4 PLC ±.0020 ANGLES ±°		NAME VERTICAL RECEPTACLE W/ P+S MULTI-BEAM XLE	
MATERIAL		APVD S_ZHAO 18JUN2008		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
FINISH		PRODUCT SPEC 108-2292		A 100779 © 6450862	
		APPLICATION SPEC 114-13251		SCALE 2:1 SHEET 4 OF 9 REV D7	
		WEIGHT -			
		CUSTOMER DRAWING			


PART NUMBER	ROWS		SIGNAL						POWER							
			5	4	3	2	1	P6	P5	P4	P3	P2	P1			
I-6450862-6	D		AP	AP	AP	AP	AP		GP		GP		GP		GS	
	C		AP	AP	AP	AP	AP									
	B		AP	AP	AP	AP	AP									
	A		AP	AP	AP	AP	AP									
6P + 20S																




PART NUMBER	ROWS		SIGNAL								POWER											
			8	7	6	5	4	3	2	1	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1		
1-6450862-5	D		AP	AP	AP	AP	AP	AP	AP	AP	GS	GS	GS	GS	GS	GS	GS	GS	GS	GS		
	AP		AP	AP	AP	AP	AP	AP	AP													
	AP		AP	AP	AP	AP	AP	AP	AP													
	AP		AP	AP	AP	AP	AP	AP	AP													
10HDP + 32S																						



PART NUMBER	ROWS		SIGNAL							POWER										
			6	5	4	3	2	1	P11	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1	
1-6450862-8	D		AP	AP	AP	AP	AP	AP												
	C		AP	AP	AP	AP	AP	AP												
	B		AP	AP	AP	AP	AP	AP												
	A		AP	AP	AP	AP	AP	AP												
11HDP + 24S																				

4805 (3/11)

[illegible][illegible]

2-6450862-2 AND 2-6450862-3 PCB LAYOUT

4805 (3/11)

[illegible]4805 (3/11)