

D

C

B

A

D

C



B

A




© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-21-102045	13APR2021	T.Q	N.S




1. MATERIAL:
1.1 HOUSING: HALOGEN FREE PLASTIC, HIGH TEMP, BLACK ,UL94V-0.
1.2 CONTACT: COPPER ALLOY
1.3 FITTING NAIL: COPPER ALLOY
- 2.1 TERMINAL:
TYPE A: 50u" MIN. NICKEL UNDERPLATING OVERALL.
50u" MIN. MATT TIN PLATING ON CONTACT AREA AND SOLDER AREA.
TYPE B: 50u" MIN. NICKEL UNDERPLATING OVERALL.
GOLD FLASH PLATING ON CONTACT AREA.
GOLD FLASH PLATING ON SOLDER AREA.
TYPE C: 50u"MIN. NICKEL UNDERPLATING OVERALL.
30u"GOLD PLATING ON CONTACT AREA.
GOLD FLASH PLATING ON SOLDER AREA
- 2.2 FITTING NAIL: 50u" MIN. NICKEL UNDERPLATING OVERALL.
1:GOLD PLATING ON SOLDER AREA.
3. REFLOW SOLDER CAPABLE TO 260°C PER ACES SPEC.
4. PACKAGE STYLE: TAPE AND REEL WITH MYLAR.




SECTION
X-X

15.4	15.0	17.0	14.0	15	5-2367197-5	3-2367197-5	1-2367197-5
14.4	14.0	16.0	13.0	14	5-2367197-4	3-2367197-4	1-2367197-4
13.4	13.0	15.0	12.0	13	5-2367197-3	3-2367197-3	1-2367197-3
12.4	12.0	14.0	11.0	12	5-2367197-2	3-2367197-2	1-2367197-2
11.4	11.0	13.0	10.0	11	5-2367197-1	3-2367197-1	1-2367197-1
10.4	10.0	12.0	9.0	10	5-2367197-0	3-2367197-0	1-2367197-0
9.4	9.0	11.0	8.0	9	4-2367197-9	2-2367197-9	2367197-9
8.4	8.0	10.0	7.0	8	4-2367197-8	2-2367197-8	2367197-8
7.4	7.0	9.0	6.0	7	4-2367197-7	2-2367197-7	2367197-7
6.4	6.0	8.0	5.0	6	4-2367197-6	2-2367197-6	2367197-6
5.4	5.0	7.0	4.0	5	4-2367197-5	2-2367197-5	2367197-5
4.4	4.0	6.0	3.0	4	4-2367197-4	2-2367197-4	2367197-4
3.4	3.0	5.0	2.0	3	4-2367197-3	2-2367197-3	2367197-3
DIM .D	DIM .C	DIM ,B	DIM .A	POS. NO.	TYPE C	TYPE B	TYPE A
PLATING SPEC.							
P/N							



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.35
2 PLC ± 0.25
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 2°





FINISH

-

DWN	18DEC2019
CHK	Tommy Qian
APVD	Wenke He
PRODUCT SPEC	Wenke He
APPLICATION SPEC	108-115169
WEIGHT	114-115031
CUSTOMER DRAWING	

TE Connectivity			
1.0P WTB BOARD SIDE VERTICAL TYPE WITH LATCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2367197	-
SCALE		SHEET	REV
N/A		1 OF 2	A1

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



Note:
PACKAGE FOR x-2367197-x
Quantity: 1400pcs/reel
14000pcs/box.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 18DEC2019	 TE Connectivity		
		CHK Wenke He			
DIMENSIONS: mm		APVD Wenke He	NAME 1.0P WTB BOARD SIDE VERTICAL TYPE WITH LATCH		
		PRODUCT SPEC 108-115169			
		APPLICATION SPEC 114-115031			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2367197
MATERIAL SEE NOTE		FINISH -	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE N/A		
			SHEET 2 of 2		
			REV A1		