



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C	WIRE SIZE EXTENDED TO 16.5AWG	11NOV2019	JA	PKS

D




C




B

A



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT TERMINATES A SINGLE MAGNET WIRE ONLY. COPPER REANGE: 0.91–1.20mm [#19–#16.5] AWG. ALUMINUM RANGE: 0.95–1.20mm [#18.5–#16.5] AWG. ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.

4 PREPRODUCTION – FASR REQUIRED



D

C

1742035

B

A

4	1742035-1
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 09DEC2003 MICHAEL S. FEHER		TE Connectivity		
DIMENSIONS: mm [INCHES]			CHK 09DEC2003 KURT A. RANDOLPH	APVD 09DEC2003 KURT A. RANDOLPH			
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
			0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-2012		
MATERIAL 082 PRE-MILLED BRASS			FINISH 0.002032[.000080] MIN TIN PLATE		APPLICATION SPEC 114-2046		
			WEIGHT -		SIZE A2		
CUSTOMER DRAWING					CAGE CODE 00779		
					DRAWING NO 1742035		
					RESTRICTED TO -		
					SCALE 10:1		
					SHEET 1 OF 1		
					REV C		