




LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
			C1	REVISED PER ECO-12-003973	05JUN2012	KH	AS	

- 1

HOUSING: LCP, UL94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE.
- 2

CONTACT: 0.76µm GOLD PER ASTM B 488 IN CONTACT AREA,
1.27µm MIN TIN-LEAD
ON PCB TAIL,
OVER 1.27µm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST: 1.27µm MIN NICKEL.
- 4

CONTACT: 0.76µm GOLD PER ASTM B 488 IN CONTACT AREA,
0.50µm MIN MATTE TIN PER ASTM B 545
ON PCB TAIL,
OVER 1.27µm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST: 1.27µm MIN NICKEL.
- 6

POWER PIN PAIRS INDICATED ARE COMMONED INSIDE ASSEMBLY.

4	9 SINGLE END, NONSEQUENTIAL WAFERS AND 7 POWER WAFER	1410997-2
2	9 SINGLE END, NONSEQUENTIAL WAFERS AND 7 POWER WAFER	1410997-1
FINISH	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO 25JUL2006	TE Connectivity	
DIMENSIONS:		CHK G. GRIFFITH 25JUL2006		
mm		APVD G. GRIFFITH 25JUL2006	NAME RIGHT ANGLE PLUG ASSEMBLY, LEFT END, FULL, 25.4mm, POWER COMBINATION, MULTIGIG RTI, DAUGHTERCARD CONNECTOR	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
9 PLC ±0		108-2072	RESTRICTED TO	
3 PLC ±0.13		APPLICATION SPEC	A100779C=1410997	
5 PLC ±0.013		114-13056	WEIGHT	
4 PLC ±			CUSTOMER DRAWING	
ANGLES ±1°			SCALE 8:1 SHEET 1 OF 1 REV C1	
FINISH 2				