




NUT



RECOMMEND PANEL CUT-OUT



NOTE:

MATERIAL

HOUSING: PA UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
SHELL: BRASS
O-RING: EPDM, BLACK
X-SHELL: ZINC ALLOY

FINISH

CONTACT: GOLD 10 μ MIN.
OVER 50 μ NICKEL
NUT: NICKEL PLATED
SHELL: NICKEL PLATED
X-SHELL: NICKEL PLATED

ELECTRICAL

RATED CURRENT: 0.5A
RATED VOLTAGE: 50VAC/60VDC
INSULATION RESISTANCE: 100 M Ω hms MIN.
CONTACT RESISTANCE: 10 m Ω hms MAX.
WATER PROOF: IP67


ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

860-X08-213R004

3 = BRASS/NICKEL SHELL & NUT
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH
4 = 10 μ GOLD



RECOMMEND P.C.B LAYOUT

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 08-12-16

NorComp

SCALE: NTS SHEET 1 OF 1 REV 5

DWG NO. 860-X08-213R004