




| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| | O | RELEASED | 12JAN2004 | SW | HW |
| | A | REVISED PER ECO-18-008968 | 11JUN2018 | RS | MZ |
| | | | | | |
| | | | | | |



- 1 NOMINAL WALL THICKNESS, EXPANDED.
- 2 EXPANDED INSIDE DIAMETER.
- 3 .250 MAXIMUM RECOVERED INSIDE DIAMETER.
4. ASSEMBLY WILL PASS ONE POUND PER SQ INCH WATER PRESSURE TEST.
5. TUBING SHRINK TEMPERATURE: 250°F.
6. OPERATING TEMPERATURE: -67°F TO 230°F.
7. THIS PART WILL ACCOMODATE Ø.250-Ø.600 CABLE RANGE.

1546921-1

PART
NUMBER

| | | | | | | | | |
|---|--|---|-------------------------------------|---|--|------------------|------------|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN S. WELDON CHK H. WAKEEM APVD H. WAKEEM | 12JAN2004 12JAN2004 12JAN2004 |  TE Connectivity | | | | |
| DIMENSIONS: INCHES | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | NAME STRAIN RELIEF ASSEMBLY, SIZE 11, MINI CPC | | | | |
|  | | PRODUCT SPEC - | | SIZE | | CAGE CODE | DRAWING NO | RESTRICTED TO |
| | | APPLICATION SPEC - | | A200779 | | C=1546921 | | - |
| MATERIAL - | | FINISH - | | WEIGHT - | | CUSTOMER DRAWING | | |
| | | | | SCALE 4:1 | | SHEET 1 OF 1 | | REV A |