

S11LOC-P04PJH0-7200  
series\_l, type\_s1



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S11LOC-P04PJH0-7200 |
| Termination       | crimp               |
| Size              | 1                   |
| Locking principle | push                |
| Coding            | 0_key               |
| Cable Diameter    | cable_mini_72       |
| Cable outlet      | standard            |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.

**CODING:** 0 °

**POSITIONS:** 4 Positions

**DIMENSIONS**

The pin layout corresponds to the view on the termination area

Contact insert description

|                    |              |
|--------------------|--------------|
| Number of contacts | 4            |
| Contact type       | pins         |
| Contact diameter   | 09mm         |
| Insulator material | peek         |
| Wire cross section | 20-24_awg    |
| Termination        | crimp        |
| Data transmission  | ethernet_100 |

reverse\_gender\_on\_request

Technical information

|                                          |         |               |
|------------------------------------------|---------|---------------|
| Max. creepage and air clearance distance | 07_mm   | 11_mm         |
| Nominal current single contact           | 10_a    | iec_60512_5_2 |
| Nominal current insert                   | 10 A    | vde_0298_4    |
| Test voltage                             | 1_kv_ac | sae_13441     |

safety\_text

Mechanical and environmental data

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip50     |
| Operating temperature | 40_120_c |
| Mating cycles         | 5000     |

mated\_unmated

Material and surface treatments

|         |               |
|---------|---------------|
| Housing | m_chrome      |
| Contact | cu_alloy_gold |

safety\_text\_2  
data\_text  
ul\_text  
illustrative\_text