



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑥ TO BE 3 TO 3.5 N·m.
  - 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑩ TO BE 0.2 TO 0.25 N·m.
  - 3 ROTATION EXAMPLES OF REF. NOS. ① AND ⑥ ARE SHOWN.
  - 4 SCREW OF REF. NO. ①, ⑥, ⑩, LOCTITE 263, OR EQUIVALENT, HENKEL JAPAN IS RECOMMENDED TO PREVENT FROM LOOSENING.
  - 5 THIS PRODUCT TO BE USED WITH CABLECLAMP, JR16WCC-※(31).  
※ DESIGNATE DIAMETER OF APPLICABLE CABLE.

5	PHOSPHOR BRONZE	NICKEL PLATING	10	STAINLESS STEEL	
4	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	9	NBR	(BLACK)
3	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	8	NBR	(BLACK)
2	COPPER ALLOY	SILVER PLATING 3μm min.	7	BRASS	BLACK CHROME PLATING
1	ALUMINUM ALLOY	BLACK CHROME PLATING	6	BRASS	BLACK CHROME PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS	
HRS		HIROSE ELECTRIC CO., LTD.	APPROVED : HY. KOBAYASHI	18. 02. 22	DRAWING NO. EDC-110562-31-00
			CHECKED : HY. KOBAYASHI	18. 02. 22	PART NO. JR16WP-10P(31)
			DESIGNED : TH. KAMEYA	18. 02. 22	CODE NO. CL114-2004-3-31
			DRAWN : MK. INOUE	18. 02. 13	