




10 9 8 7 6 5 4 3 2 38779




REF -50 OPTION SCREW (WHERE APPLICABLE)



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. DIMENSION SHOWN IN MM/INCH.
4. *XX* REFERS TO THE QUANTITY OF CIRCUITS.
5. ASSEMBLY IS ROHS COMPLIANT.

NO. OF CIRCUITS *XX*	DIM. "A"		DIM. "B"		ASSEMBLY MATERIAL NO. (STANDARD)	ASSEMBLY MATERIAL NO. (-50 OPTION)
2	21.3	.84	9.53	.375	387790231	387790371
3	30.8	1.21	19.05	.750		387790140
4	40.3	1.59	28.58	1.125		387790250
5	49.8	1.96	38.10	1.500		387790031
6	59.4	2.34	47.63	1.875	387790004	387790369
7	68.9	2.71	57.15	2.250	387790052	
8	78.4	3.09	66.68	2.625		387790142
9	87.9	3.46	76.20	3.000		387790224
10	97.5	3.84	85.73	3.375	387790091	



5	XX	SCREW, #6-32X.250 PAN HD, PHIL-SLOT W/WSHR (-50 OPTION)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW, #6-32X.250, BGHD PHIL-SLOT (STANDARD)	STEEL	ZN, CLEAR CHROMATE
3	XX	TERMINAL, SOLDER Y	BRASS	TIN PLATE
2	XX	TERMINAL PLATE	BRASS	NICKEL PLATE
1	1	INSULATOR, NO MTG.	PBT	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

UPDATE TERM. TAIL DIM/TOL.
EC NO: WNA2012-0134
DRAWN: JENC INAS 2011/10/11
CHKD: JMACNEIL 2011/10/11
APPR: JMACNEIL 2011/10/17

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .005
2 PLACES ± 0.13 ± .01
1 PLACE ± 0.3 ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
C. YORK 2006/10/25
CHECKED BY DATE
J. MACNEIL 2006/10/25
APPROVED BY DATE
J. MACNEIL 2006/10/25
MATERIAL NO.
SEE CHART

SCALE
2:1
DESIGN UNITS
INCH
THIRD ANGLE PROJECTION
9.53/.375 DOUBLE ROW
LOW PROFILE BTS ASSY,
NO MTG.
MOLEX INCORPORATED
DOCUMENT NO.
SD-38779-006
SHEET NO.
1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION