


Actuator

704.010.0



<https://eao.com/p/704.010.0>

Your product:



704.010.0
Actuator

FRONT

Front form:	round
Front bezel material:	Plastic
Front dimension:	Ø 29 mm
Front bezel colour:	Grey

MOUNTING

Design:	raised
----------------	--------

OPERATING-/INDICATION PART

Lens shape:	flush
Lens illumination:	non illuminative
Lens colour:	Black
Lens optics:	opaque
Lens material:	Plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	-------------------------------------------------------------------------------------------

MECHANICAL CHARACTERISTIC

Operating force:	8 N
Switching action:	Momentary
Mechanical lifetime:	≤3 Mio. cycles of operation


Weight: 0.04 kg
Operating Travel: ca. 5.8 mm \pm 0.2 mm

AMBIENT CONDITION

IP Protection: IP65 front side
Storage temperature: – 40 °C ... + 85 °C
Operating temperature: – 40 °C ... + 55 °C


OTHER

Housing colour: Grey
Hints: Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on
Short Description: Actuator, Ø 29 mm, flush, non illuminative, Black, Plastic, opaque, round, Grey, Plastic, Momentary
Housing material: Plastic
max. number of switching elements: 3
Dimension drawings:



A = Screw terminal

Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Wiring diagrams:

E---