

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

LOC1DIST2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST ISSUE	28FEB2010	AV	GT
	AI	REVISED PER ECR-13-009678	18SEP2013	RS	DD

TYPICAL APPLICATION

HIGH VOLTAGE

KEYING HV-2

KEYING HV-3

KEYING HV-4

KEYING HV-5

LOW VOLTAGE

KEYING LV-2

MATERIALS:

1) CONTACTS: SOLDERING SIDE TIN PLATED Ph. BRONZE

RECEPTACLE IN SPECIAL ALLOY COPPER TIN PLATED

HOUSING: PBT 15%GFF UL 94 V0 COLOR WHITE

2

P/N 293655-1 POLARIZATION KEY HV-2

TO BE USED FOR FOR SWITCH APPLICATION ONLY

PRINTED CIRCUIT BOARD LAYOUT FOR HIGH VOLTAGE VERSION

TOLERANCES UNLESS OTHERWISE SPECIFIED ± 0.05

PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL

PRINTED CIRCUIT BOARD LAYOUT FOR LOW VOLTAGE VERSION

TOLERANCES UNLESS OTHERWISE SPECIFIED ± 0.05

PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL

TE Connectivity

7,5 mm PCB CONNECTOR ASSEMBLY STRAIGHT FEMALE VERSION FOR USA MARKET

SIZE: A300779 CAGE CODE: C-293655 DRAWING NO: 108-20294 APPLICATION SPEC: 114-32102 WEIGHT: -

Customer Drawing

SCALE: 5:1 SHEET: 1 OF 1 REV: AI