






LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
		B		REVISED PER ECO-11-025276	04JAN12	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. K. SHOBER	04JAN12	 TE Connectivity		
			CHK	J. EABY	04JAN12			
			APVD	J. EABY	04JAN12	NAME		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		IMPACT, 2 PAIR, 10 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.36 PTH		
mm				APPLICATION SPEC				
		0 PLC ±.25						
		2 PLC ±0.13						
		3 PLC ±.1						
		4 PLC ±.1						
ANGLES		±.1				SIZE		
		FINISH		WEIGHT		CAGE CODE		
		SEE TABLE		-		DRAWING NO		
MATERIAL				CUSTOMER DRAWING		RESTRICTED TO		
						A100779C-2057421		
				SCALE		6:1		
						SHEET		
						1 OF 2		
						REV B		

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057421-6
	4.9	2057421-5
	4.5	2057421-4
	5.5	2057421-3
	4.9	2057421-2
	4.5	2057421-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER	04JAN12	 TE Connectivity		
DIMENSIONS:		CHK J. EABY	04JAN12			
mm		APVD J. EABY	04JAN12	NAME	IMPACT, 2 PAIR, 10 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.36 PTH	
		PRODUCT SPEC				
		APPLICATION SPEC				
		WEIGHT				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
9 PLC ±		A100779		C=2057421		-
1 PLC ±0.25		SCALE		5:1	SHEET	2
2 PLC ±0.13		OF		2	REV	B
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						
SEE TABLE						