









P.C.B.HOLE DRILLINGS



NOTES:

- METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- COAXIAL CONTACTS 50 OHM: COPPER ALLOY
PLATING INNER CONDUCTOR: 50µm HARD GOLD over min. 50µm NICKEL
PLATING OUTER CONDUCTOR: 30µm HARD GOLD over min. 50µm NICKEL
- METAL BRACKET: ZINC DIE CAST; 300µm COPPER/ 40-120µm NICKEL/ 120-200µm TIN
- THREADED INSERT: COPPER ALLOY; min 200µm TIN over 80µm NICKEL
- PCB-SNAP: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1,6mm
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3003W3PXX78N40X CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		dim. in mm	scale: 2:1(5:1)	
				date			material: SEE NOTES	
				name			title:	
				drawn: 27.08.2007 Sonnenberg			D-SUB COMBINATION MALE	
DO NOT ALTER CAD DRAWING BY HAND				appd. 27.08.2007 Mickenbecker		norm	3W3P	
				d-old			with threaded insert ,metal bracket and snap	
				a Origin			dwg no: Inventor 10	
				rev. description date name			13K1A2207	
				CONEC			part no: 3003W3PXX78N40X	
							DIN-A3 sh: 1	