






LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
				A		REV PER ECO-11-007577	13APR2011	RKC	JE	
				B		REVISED PER ECO-16-008845	17SEP2016	AP	RP	
				C		REVISED PER ECO-17-006073	05JUN2017	AP	RP	



- REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- MATERIAL:
SHIELD - PHOSPHOR BRONZE
CONTACT - COPPER-NICKEL-SILICON
HOUSING, CHICKLET AND CHICKLET COVER - GLASS FILLED POLYESTER
- FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5 μ m MIN MATTE TIN OVER BASE PLATING
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN
- DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

RECOMMENDED PC BOARD LAYOUT, DAUGHTER BOARD, COMPONENT SIDE SHOWN
SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S. J. MAGARO	04MAR2005	TE Connectivity RECEPTACLE ASSEMBLY, 2 PAIR, 25mm, HMZd			
DIMENSIONS:		CHK	R. A. PATTERSON	04MAR2005				
mm		APVD		-				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		-	NAME		SIZE	
0 PLC		1 PLC		±	APPLICATION SPEC		CAGE CODE	
2 PLC		3 PLC		±	DRAWING NO		RESTRICTED TO	
4 PLC		ANGLES		±	WEIGHT		A100779	
MATERIAL		FINISH		±	CUSTOMER DRAWING		SCALE	
2		3		±	8:1		SHEET	
					1		OF	
					1		REV	
					C			