


Actuator

704.118.018



<https://eao.com/p/704.118.018>

Your product:



704.118.018 Actuator

FRONT

Front bezel colour:	Nature
Front dimension:	Ø 35 mm
Front bezel material:	Aluminium

MOUNTING

Mounting cut-out:	Ø 30.5 mm
Design:	flush

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching angle:	42° left / 42° right
Weight:	0.099 kg
Mechanical lifetime:	≤50 000 cycles of operation
Switching positions:	3 positions
Switching action:	Momentary - Rest (a) - Maintained

AMBIENT CONDITION

Storage temperature: – 40 °C ... + 85 °C

IP Protection: IP65 front side

Operating temperature: – 40 °C ... + 55 °C


OTHER

Short Description: Actuator, Ø 30.5 mm, Ø 35 mm, Nature, Aluminium, Momentary - Rest (a) - Maintained


max. number of switching elements: 3

Hints: The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on

Switching positions:



Dimension drawings:




A = Screw terminal

Wiring diagrams:



Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm