

## Coaxial Cable Connector 25\_BNC-75-2-8/133\_N

### Description

Straight panel cable jack, flange mount

Interface standards

Interface compatible with IEC 61169-8



### Technical Data

#### Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0168 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00071040
Catalogue drawing	DCA-00008807
Assembly instruction	DOC-0000179123

### Ordering Information

Single package	25_BNC-75-2-8/133_NE
----------------	----------------------

### Additional Information

Suitable cables	RG_179_B/U, ENVIROFLEX_179, RG_187_A/U
-----------------	--