



DO NOT SCALE
FROM THIS PRINT

FIG 1

THROUGH HOLE/STRAIGHT MODIFIED

DIFFERENT AS SHOWN OTHERWISE SAME AS FIG. 1





FIG 2

-02: SURFACE MOUNT

UNLESS OTHERWISE NOTED		
DIMENSIONS ARE IN INCHES		TOLERANCES ARE:
ONE PLACE DECIMALS: ± .1 [3]	THREE PLACE DECIMALS: ± .005 [.13]	ANGLES: ± 2°
TWO PLACE DECIMALS: ± .01 [.3]	FOUR PLACE DECIMALS: ± .0020 [.051]	

TITLE: .050 [1.27] C.L.
SOCKET STRIP
SINGLE ROW ASSEMBLY

DWG NO:

SFM-1XX-XX-XX-S-XX
SHEET 1 OF 3

SFM-1XX-XX-XX-S-XX

NO. OF POSITIONS

ALL POSITIONS AVAILABLE

-2 THRU -50

USE BODY: (SFM-XX-S-XX-X)

LEAD STYLE

-01: THROUGH HOLE
USE CONTACT: (C-44-01-XX)
(SEE FIG. 1)-02: SURFACE MOUNT
USE CONTACT: (C-44-02-XX)
(SEE FIG. 2)-03: STRAIGHT MODIFIED
USE CONTACT: (C-44-03-XX)
(SEE FIG. 1)-L1: THROUGH HOLE (LOW INSERTION)
USE CONTACT: (C-61-01-XXX)
(SEE FIG. 1)-L2: SURFACE MOUNT (LOW INSERTION)
USE CONTACT: (C-61-02-XXX)
(SEE FIG. 2)-L3: STRAIGHT MODIFIED (LOW INSERTION)
USE CONTACT: (C-61-03-XXX)
(SEE FIG. 1)-T1: THROUGH HOLE (PHOS BRONZE)
USE CONTACT: (C-119-01-XXX)
(SEE FIG. 1)-T2: SURFACE MOUNT (PHOS BRONZE)
USE CONTACT: (C-119-02-XXX)
(SEE FIG. 1)

- OPTIONS

(LEAVE BLANK FOR STANDARD

AND USE SFM-XX-S-LC-X)

-N: NO POLARIZATION NOTCH

(USE SFM-XX-S-XX-N)

-A: ALIGNMENT PIN (USE SFM-XX-S-A-X)

(SEE FIGURE 3)

-LC: LOCKING CLIP (SEE FIGURE 5) (SEE NOTE 5)

(USE (2) LC-05-TM & SFM-XX-S-LC-X)

-P: PICK AND PLACE PAD (SEE FIGURE 4)

(USE PPP-14)

-K: POLYAMIDE FILM (SEE FIG. 6, SHT. 2)

-TR: TAPE AND REEL (-X2 LEAD STYLE ONLY)

* -SN: SOLDER NAIL

(SEE SHT. 3, FIG. 7)

BODY SPECIFICATION

-S: SINGLE ROW

PLATING SPECIFICATION

-S: 30μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

-F: 3μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

-L: 10μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

-SM: 30μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

-FM: 3μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

-LM: 10μ SELECTIVE GOLD IN CONTACT AREA,

MATTE TIN ON TAIL

* = NOT TOOLED

-LM: SELECTIVE LIGHT GOLD

-SPECIFY -L IN PLATING SUFFIX -X/

MATTE TIN TAILS

(USE C-XX-XX-L)

TABLE 1

SUFFIX	TAIL LENGTH "A"	TAIL WIDTH "B"
-01,-L1	.120 [3.05]	.020 [.51]
-03,-L3	.075 [1.91]	.016 [.41]

NOTES:

1. MIN. PUSHOUT FORCE: .5 lb.

2. COPLANARITY TO BE WITHIN .004 [.10].

3. (C) REPRESENTS CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL.

4. TUBE ALL POSITIONS.

5. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.

MATERIAL:

INSULATOR:
LCP, UL 94 VOCONTACT:
BeCuEXISPROD\ASSEMBLY\050
SFMASMS1

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322MADE BY: REIDINGER 9-8-92
CHECKED BY: MCCARTINENG.
APPROVAL
DEMSFM-1XX-XX-XX-S-XX
SHEET 1 OF 3

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC, MECHANICAL, PHOTOCOPYING,
RECORDING, OR BY ANY INFORMATION
SYSTEMS WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC INC.