



| ▲ SWITCH FUNCTION |          |          |
|-------------------|----------|----------|
| POS. 1            | POS. 2   | POS. 3   |
|                   |          |          |
| ON                | ON       | ON       |
| 2-3, 5-6          | 2-3, 5-4 | 2-1, 5-4 |



DPDT 3 WAY CIRCUIT  
NOTE: JUMPER PIN 3 TO 5

## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. PLATING MATERIAL: SILVER
5. RATING: 5A MAX. @ 120 VAC or 28VDC, 2A @ 250 VAC
6. ELECTRIC LIFE: 40,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. HARDWARE TO BE SHIPPED BULK:  
T100011 - LOCK WASHER, QTY 1  
T100002 - LOCK RING, QTY 1  
T100000 - HEX NUT, QTY 2



|     |        |                         |         |    |
|-----|--------|-------------------------|---------|----|
| B   | 23506  | correct Switch Function | 8/1/18  | MW |
| A   | 23405  | New Release             | 6/14/18 | MW |
| REV | PCR NO | DESCRIPTION             | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 100DP6T6B15M3QEH

|              |                   |          |                 |          |
|--------------|-------------------|----------|-----------------|----------|
| SCALE<br>2:1 | DATE<br>6/14/2018 | DR<br>MW | DWG<br>ST126069 | REV<br>B |
|--------------|-------------------|----------|-----------------|----------|