
RECOMMENDED P.C.B. LAYOUT



CIRCUIT: SPDT

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
ON	OFF	<ON>
2-3	OPEN	2-1


< >=Momentary

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 5A @120VAC or 28VDC;
2A @250VAC
- FIXED TERMINAL/MOVING CONTACT:
Copper Alloy W/Silver Plate.
- ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
- INSULATION RESISTANCE: 1,000M ohm min.
- DIELECTRIC STRENGTH: 1000V RMS @sea level
- OPERATING TEMP.: -30°C to +85°C

NO EPOXY ON TERMINALS
BELOW SURFACE C

-C-

**E-SWITCH®**

C	23647	DIM FROM 6.35 TO 6.60	10/30/18	MJR
B	12194	REVISED AND REDRAWN	6/4/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE

100 SP-5 T1 B1 M2 Q E

SCALE

2:1

DATE

6/4/02

DR

CJB

DWG

T115003

REV

C