




FINISH	E	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER
11	9/10	65.33 [2.572]	32.66 [1.286]	66.59 [2.622]	64.05 [2.522]	49	100
11	9/10	58.98 [2.322]	29.48 [1.161]	60.24 [2.372]	57.70 [2.272]	44	90
11	9/10	52.63 [2.072]	26.31 [1.036]	53.89 [2.122]	51.35 [2.022]	39	80
11	9/10	46.28 [1.822]	23.13 [.911]	47.54 [1.872]	45.00 [1.772]	34	70
11	9/10	39.93 [1.572]	19.96 [.786]	41.19 [1.622]	38.65 [1.522]	29	60
11	9/10	33.58 [1.322]	16.78 [.661]	34.84 [1.372]	32.30 [1.272]	24	50
11	9/10	27.23 [1.072]	13.61 [.536]	28.49 [1.122]	25.95 [1.022]	19	40
11	9/10	20.88 [.822]	10.43 [.411]	22.14 [.872]	19.60 [.772]	14	30
11	9/10	14.53 [.572]	7.26 [.286]	15.79 [.622]	13.25 [.522]	9	20
11	9/10	8.18 [.322]	4.08 [.161]	9.44 [.372]	6.90 [.272]	4	10
15	1/5	65.33 [2.572]	32.66 [1.286]	66.59 [2.622]	64.05 [2.522]	49	100
15	1/5	58.98 [2.322]	29.48 [1.161]	60.24 [2.372]	57.70 [2.272]	44	90
15	1/5	52.63 [2.072]	26.31 [1.036]	53.89 [2.122]	51.35 [2.022]	39	80
15	1/5	46.28 [1.822]	23.13 [.911]	47.54 [1.872]	45.00 [1.772]	34	70
15	1/5	39.93 [1.572]	19.96 [.786]	41.19 [1.622]	38.65 [1.522]	29	60
15	1/5	33.58 [1.322]	16.78 [.661]	34.84 [1.372]	32.30 [1.272]	24	50
15	1/5	27.23 [1.072]	13.61 [.536]	28.49 [1.122]	25.95 [1.022]	19	40
15	1/5	20.88 [.822]	10.43 [.411]	22.14 [.872]	19.60 [.772]	14	30
15	1/5	14.53 [.572]	7.26 [.286]	15.79 [.622]	13.25 [.522]	9	20
15	1/5	8.18 [.322]	4.08 [.161]	9.44 [.372]	6.90 [.272]	4	10

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG KATE HELM 08/07/91		CHK D. GORENC 8/12/91		NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC	
0 PLC ± -		1 PLC ± -		2 PLC ± 0.13 [005]		3 PLC ± -	
4 PLC ± -		ANGLES ± ° 30'		WEIGHT		SIZE	
MATERIAL: HOUSING: LCP, COLOR-BLACK POST: PINS: BRONZE HOLD DOWN: COPPER ALLOY		FINISH: SEE TABLE		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV J3	

TE Connectivity

HEADER ASSEMBLY, SURFACE MOUNT, AMPMODU 50/50 GRID (8.12[.320] MATED HEIGHT)

108-1332

114-7010

00779

104656