





SCALE 4:1


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AG	00		2	Modified DIA to M6 Hex. Customer Request.	19JAN2010	D.YI	D.YI
			3	CHANGED TOLERANCE ON DIMENSION LOC: C4	10AUG2010	DH	DY
			A	REVISED PER ECO-10-016889	02SEP2010	DH	DY

- 1 MATERIAL: ZINC ALLOY DIE CASTING.
- 2 FINISH: CHROMATE CONVERSION COATING.
(ROHS COMPATIBLE).
- 3 M6 HEX NUT SIZE
USE 10MM SOCKET OR WRENCH FOR FIXTURING



RECOMMENDED P.C. BOARD LAYOUT

2.20	27.0	36.2	1645546-6
1.70	30.0	39.2	1645546-5
1.70	18.0	27.2	1645546-4
1.70	6.0	15.2	1645546-3
1.70	3.0	12.2	1645546-2
1.70	27.0	36.2	1645546-1
DIM D	DIM C	DIM A	Part Number

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN D.YI 02-Sep-10		 Tyco Electronics Harrisburg, PA 17105-3608					
DIMENSIONS: mm 				CHK D.YI 06 JAN 10		NAME MODULE, VERTICAL FEMALE UNIVERSAL POWER MODULE -					
				APVD D.YI 06 JAN 10							
				PRODUCT SPEC -							
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.013 4 PLC ± ANGLES ±30° FINISH				APPLICATION SPEC -						SIZE CAGE CODE DRAWING NO RESTRICTED TO	
				WEIGHT -							
				CUSTOMER DRAWING							
MATERIAL  -				-		A200779		C-1645546		-	
						SCALE 3:1		SHEET 1 OF 1		REV A	