






ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



SCALE 2:1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

CHARACTERISTICS

OPERATING FORCE AT ROLLER- - - -16 OZ MAX
RELEASE FORCE AT PLUNGER- - - -5 OZ MIN
PRETRAVEL- - - - -115 MAX
DIFFERENTIAL TRAVEL- - - - .058 MAX
OVERTRAVEL- - - - - .025 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SPNO-DB

10 AMP 125/250 VAC
7.5 AMP 28 VDC IND

SEALED WITH
EPOXY POTTING
COMPOUND

NOTES

1. SWITCH SEALED PER MIL-PRF-8805 SYMBOL 3, WATERTIGHT
2. BASIC SWITCH MIL-PRF-8805/7 TYPE
3. STAINLESS STEEL PLUNGER & ROLLER
4. ENCLOSURE TO MEET REQ. OF U.S. ARMY TANK AUTOMOTIVE COMMAND NO. 7748750
5. ROLLER ARM IS PHOS. BRONZE