


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		D1	ADD NEW PART	21MAR2013	OL	SZ




1. HOUSING: GLASS FILLED LIQUID CRYSTAL POLYMER, COLOR: BLACK, UL 94 V-O RATED
SIGNAL CONTACT: PHOSPHOR BRONZE
SIGNAL OVERMOLD: GLASS FILLED POLYESTER
POWER CONTACT: COPPER ALLOY
BOARD LOCKS: PHOSPHOR BRONZE
2. SIGNAL CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00076mm MIN GOLD OR 0.00008mm MIN GOLD OVER
0.00076mm MIN PALLADIUM-NICKEL
TAIL AREA: 0.0005mm MIN MATTE TIN


POWER CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00076mm MIN GOLD OR
0.00008mm MIN GOLD OVER 0.00076mm MIN PALLADIUM-NICKEL,
TAIL AREA: 0.0005mm MIN MATTE TIN

BOARD LOCKS: 0.00076mm MIN MATTE TIN OVER 0.00127mm MIN NICKEL.
3. CONTACT MATING AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
4. THIS CONNECTOR EMPLOYS UL RECOGNIZED Z-PACK 2mm HM SIGNAL CONTACTS

5. DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER.
6. PC BOARD THICKNESS 1.4mm MIN, FOR WAVE SOLDER PC BOARD THICKNESS 2.62 MAX
7. SEE APPLICATION SPEC 114-13215 FOR PLATED THROUGH HOLE INFORMATION
8. SEE CUSTOMER DRAWING 1926720 OR 1926722 FOR MATING CONNECTOR
9. UNPLATED HOLES






2-1926721-5 SHOWN

3.875	5.375	60	30	9	5	77.14	82.74	10P X 30S X 10P	3-1926721-3
3.50	5.00	48	25	7	4	63.39	68.99	8P X 25S X 8P	2-1926721-5
4.125	5.625	36	15	5	2	49.64	55.24	6P X 15S X 6P	1-1926721-6
4.125	5.625	12	15	1	2	27.64	33.24	2P X 15S X 2P	1926721-2
DIM H	DIM G	F PLACES	E PLACES	D SPACES	C SPACES	DIM B	DIM A	DESCRIPTION	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT FOR Tyco Electronics Corporation IT IS SUBJECT TO THE POLICY OF Tyco Electronics Corporation AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE WRITTEN PERMISSION OF Tyco Electronics Corporation						DWN P BRANDBERG 26NOV07 CHK N REESER 26NOV07 APVD N REESER 26NOV07		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				NAME			
mm		0 PLC ±.13 1 PLC ±.10 2 PLC ±.08 3 PLC ±.07 4 PLC ±.06 ANGLES ±.1				RECEPTACLE ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, POWER/SIGNAL/POWER, WITH BOARD LOCKS, MINIPAK HDL			
						PRODUCT SPEC 108-2325			
						APPLICATION SPEC 114-13215			
MATERIAL SEE NOTE 1		FINISH SEE NOTE 2				SIZE A1		CAGE CODE 00779	DRAWING NO C-1926721
						WEIGHT -		RESTRICTED TO -	
Customer Drawing								SCALE 4:1	SHEET 1 OF 3
								REV D	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00	-	-	SEE SHEET 1	-	-	-

TE PART NUMBER AND DATE CODE



DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH	DWN P BRANDBERG 26NOV07	Tyco Electronics Harrisburg, PA 17105-3608	
			CHK N REESER 26NOV07		
		MATERIAL SEE NOTE 1	APVD N REESER 26NOV07	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, POWER/SIGNAL/POWER, WITH BOARD LOCKS, MINIPAK HDL	
			PRODUCT SPEC 108-2325		
		FINISH SEE NOTE 2	APPLICATION SPEC 114-13215	SIZE A 100779	
			WEIGHT -		
			Customer Drawing	SCALE 4:1	SHEET 2 OF 3
				REV D1	



THIS DRAWING IS A CONTRACT DOCUMENT FOR THE TYGO ELECTRONICS CORPORATION IT IS SUBJECT TO THE TYGO ELECTRONICS CORPORATION'S STANDARD TERMS OF SALE WHICH MAY BE OBTAINED BY REQUESTING THE TYGO ELECTRONICS CORPORATION SHOULD BE CONTACTED FOR THE LATEST REVISIONS.		DWN P BRANDBERG 26NOV07		CHW N REESER 26NOV07		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$.013 3 PLC $\pm$ 4 PLC $\pm$ 4 PLC ANGLES $\pm$		NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, POWER/SIGNAL/POWER, WITH BOARD LOCKS, MINIPAK HDL		SIZE A	
		PRODUCT SPEC 108-2325		APPLICATION SPEC 114-13215		CODE NO 00779	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 2		WEIGHT -		RESTRICTED TO -	
Customer Drawing				SCALE 4:1		SHEET 3 of 3	
				REV D1			