





1 2 3 4



703 023 208 965 ...	schwarz	90 05
703 023 207 965 ...	grau	70 05
703 023 206 965 ...	blau	50 02
703 023 205 965 ...	grün	60 29
703 023 204 965 ...	gelb	10 16
703 023 203 965 ...	weiß	90 10
703 023 202 965 ...	rot	30 20
Zeichnungs-Nr.	Farbe	RAL-Nr.

703 023 2.. 965 100	9.8
703 023 2.. 965 090	8.8
703 023 2.. 965 080	7.8
703 023 2.. 965 070	6.8
703 023 2.. 965 060	5.8
703 023 2.. 965 050	4.8
703 023 2.. 965 040	3.8
Zeichnungs-Nr.	$\varnothing X$ in mm

				Allgemeintoleranzen nach DIN ISO 2768-mK Tolerierung nach DIN ISO 8015	Rohteil: Silikan LR3003/70		Rohgew.:	PE-Modell-Nr.:		
							CAD-Nr.:	00028264		
									Bl.: 1	
				2005	Tag	Name	Benennung:			Maßstab:
				Bearb.	27.01.	Lengmüller	Knickschutzfülle			3:1
d	-----	17.09.12	Hobmaier	Gepr.						
c	-----	02.03.09	Lengmüller	Norm.						
b	-----	21.03.05	Lengmüller				Zeichnungs Nr.:			Vervielf. Paus
a	-----	17.03.05	Lengmüller				703 023 2.. 965 ...			
Aend.	Aend.-Mitt.	Datum	Name	 A perfect alliance.			Ersatz fuer:			Nr.
zust.										