


**OMNIMATE Signal - series BL/SL 3.50**  
**BLZF 3.50/08/180LR SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Female connectors with tension clamp system for connecting cables in 3.50 pitch. They provide space for labelling and can be coded.

**General ordering data**

| Type         | BLZF 3.50/08/180LR SN OR BX                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Order No.    | <a href="#">1531300000</a>                                                                                                        |
| Version      | PCB plug-in connector, female plug, 3.50 mm, No. of poles: 8, 180°, Tension-clamp connection, Clamping range, max. : 1.5 mm², Box |
| GTIN (EAN)   | 4050118336405                                                                                                                     |
| Qty.         | 50 pc(s).                                                                                                                         |
| Product data | IEC: 320 V / 14.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 26 - AWG 14                                                         |
| Packaging    | Box                                                                                                                               |

## OMNIMATE Signal - series BL/SL 3.50 BLZF 3.50/08/180LR SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Technical data

#### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 34.4 mm | Width (inches)  | 1.354 inch |
| Height     | 14.5 mm | Height (inches) | 0.571 inch |
| Depth      | 29.5 mm | Depth (inches)  | 1.161 inch |
| Net weight | 7.696 g |                 |            |

#### system parameters

|                                              |                                     |                                            |                     |
|----------------------------------------------|-------------------------------------|--------------------------------------------|---------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 3.50 | Type of connection                         | Field connection    |
| Wire connection method                       | Tension-clamp connection            | Pitch in mm (P)                            | 3.5 mm              |
| Pitch in inches (P)                          | 0.138 inch                          | Conductor outlet direction                 | 180°                |
| No. of poles                                 | 8                                   | L1 in mm                                   | 24.5 mm             |
| L1 in inches                                 | 0.965 inch                          | Number of rows                             | 1                   |
| Pin series quantity                          | 1                                   | Rated cross-section                        | 1.5 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              | Touch-safe protection acc. to DIN VDE 0470 | IP 20               |
| Volume resistance                            | 5.00 mΩ                             | Can be coded                               | Yes                 |
| Stripping length                             | 10 mm                               | Screwdriver blade                          | 0.4 x 2.5           |
| Screwdriver blade standard                   | DIN 5264-A                          | Plugging cycles                            | 25                  |
| Plugging force/pole, max.                    | 7 N                                 | Pulling force/pole, max.                   | 5 N                 |

#### Material data

|                                       |                          |                                       |                     |
|---------------------------------------|--------------------------|---------------------------------------|---------------------|
| Insulating material                   | PBT                      | Colour                                | orange              |
| Colour chart (similar)                | RAL 2000                 | Insulating material group             | IIIa                |
| CTI                                   | ≥ 200                    | Insulation strength                   | ≥ 10 <sup>8</sup> Ω |
| UL 94 flammability rating             | V-0                      | GWFI                                  | 960 °C              |
| Contact material                      | Copper alloy             | Contact surface                       | tinned              |
| Layer structure of plug contact       | 4-8 μm Sn hot-dip tinned | Storage temperature, min.             | -25 °C              |
| Storage temperature, max.             | 55 °C                    | Max. relative humidity during storage | 80 %                |
| Operating temperature, min.           | -50 °C                   | Operating temperature, max.           | 100 °C              |
| Temperature range, installation, min. | -30 °C                   | Temperature range, installation, max. | 100 °C              |

#### Conductors suitable for connection

|                                                                     |                      |
|---------------------------------------------------------------------|----------------------|
| Clamping range, min.                                                | 0.13 mm <sup>2</sup> |
| Clamping range, max.                                                | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.                             | AWG 28               |
| Wire connection cross section AWG, max.                             | AWG 16               |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                                             | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                                          | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                      |
| w. plastic collar ferrule, DIN 46228 pt 4, 1 mm <sup>2</sup> max.   |                      |
| w. wire end ferrule, DIN 46228 pt 1, min 0.2 mm <sup>2</sup>        |                      |
| w. wire end ferrule, DIN 46228 pt 1, 1.5 mm <sup>2</sup> max.       |                      |
| Outer diameter of insulation, max.                                  | 2.9 mm               |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.4 mm x 1.5 mm      |

**OMNIMATE Signal - series BL/SL 3.50**  
**BLZF 3.50/08/180LR SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

|                     |                                                                                     |                  |                      |       |
|---------------------|-------------------------------------------------------------------------------------|------------------|----------------------|-------|
| Clampable conductor | Cross-section for conductor connection                                              | Type             | fine-wired           |       |
|                     |                                                                                     | nominal          | 0.5 mm <sup>2</sup>  |       |
|                     | AEH                                                                                 | Stripping length | nominal              | 12 mm |
|                     |                                                                                     | Stripping length | nominal              | 10 mm |
|                     | Cross-section for conductor connection                                              | Type             | fine-wired           |       |
|                     |                                                                                     | nominal          | 0.75 mm <sup>2</sup> |       |
|                     | AEH                                                                                 | Stripping length | nominal              | 12 mm |
|                     |                                                                                     | Stripping length | nominal              | 10 mm |
|                     | Cross-section for conductor connection                                              | Type             | fine-wired           |       |
|                     |                                                                                     | nominal          | 1 mm <sup>2</sup>    |       |
|                     | AEH                                                                                 | Stripping length | nominal              | 12 mm |
|                     |                                                                                     | Stripping length | nominal              | 10 mm |
|                     | Cross-section for conductor connection                                              | Type             | fine-wired           |       |
|                     |                                                                                     | nominal          | 1.5 mm <sup>2</sup>  |       |
|                     | AEH                                                                                 | Stripping length | nominal              | 10 mm |
| Reference text      | The outside diameter of the plastic collar should not be larger than the pitch (P). |                  |                      |       |
| Max. clamping range | 1.5 mm <sup>2</sup>                                                                 |                  |                      |       |

**Rated data acc. to IEC**

|                                                                           |        |                                                                       |                   |
|---------------------------------------------------------------------------|--------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   |        | IEC 60664-1, IEC 61984                                                |                   |
| Rated current, max. no. of poles (Tu=20°C)                                | 10 A   | Rated current, min. no. of poles (Tu=20°C)                            | 14.5 A            |
| Rated current, max. no. of poles (Tu=40°C)                                | 8 A    | Rated current, min. no. of poles (Tu=40°C)                            | 12 A              |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V  | Rated voltage for surge voltage class / pollution degree II/2         | 320 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV | Rated voltage for surge voltage class / pollution degree III/3        | 160 V             |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV            |
|                                                                           |        | Short-time withstand current resistance                               | 3 x 1s with 100 A |

**Rated data acc. to CSA**

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 26 | Wire cross-section, AWG, max.     | AWG 14 |

**Rated data acc. to UL 1059**

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 10 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26 | Wire cross-section, AWG, max.         | AWG 14 |

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 60 mm  |
| VPE width | 110 mm | VPE height | 145 mm |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC002637    | ETIM 5.0   | EC002637    |
| ETIM 6.0   | EC002638    | eClass 6.2 | 27-26-07-04 |
| eClass 7.1 | 27-44-04-02 | eClass 8.1 | 27-44-04-02 |
| eClass 9.0 | 27-44-03-09 | eClass 9.1 | 27-44-03-09 |

## OMNIMATE Signal - series BL/SL 3.50 BLZF 3.50/08/180LR SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Notes

#### Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Max. outer diameter of the conductor: 2.9 mm
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- Crimp shape A for wire-end ferrules with crimping tools PZ 1,5 (order no. 9005990000) or PZ 6/5 (order no. 9011460000) for larger wire cross-sections recommended.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

#### IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

### Approvals

#### Approvals



#### ROHS

Conform

### Downloads

#### Approval/Certificate/Document of Conformity

[Declaration of the Manufacturer](#)

#### Brochure/Catalogue

[FL DRIVES EN](#)  
[MB DEVICE MANUF. EN](#)  
[FL DRIVES DE](#)  
[FL BUILDING SAFETY EN](#)  
[FL APPL LED LIGHTING EN](#)  
[FL INDUSTR.CONTROLS EN](#)  
[FL MACHINE SAFETY EN](#)  
[FL HEATING ELECTR EN](#)  
[FL APPL INVERTER EN](#)  
[FL\\_BASE\\_STATION\\_EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)

#### Engineering Data


[STEP](#)

## OMNIMATE Signal - series BL/SL 3.50 BLZF 3.50/08/180LR SN OR BX


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Drawings


### Dimensional drawing




### Graph



### Graph



### Graph







The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG





Dimensions without tolerances are no check dimensions

The English version is binding





SHOWN:BLZF 3.50/04/180







SHOWN:BLZF 3.50/04/180F







SHOWN:BLZF 3.50/04/180/SO







SHOWN:BLZF 3.50/04/180LR REDESIGN



SHOWN:BLZF 3.50/04/180LR



SHOWN:BLZF 3.50/04/180LH



ALLGEMEINGÜLTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE  
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|                    |      |                         |
|--------------------|------|-------------------------|
| 24                 | 80.5 | 3.169                   |
| 23                 | 77.0 | 3.032                   |
| 22                 | 73.5 | 2.894                   |
| 21                 | 70.0 | 2.756                   |
| 20                 | 66.5 | 2.618                   |
| 19                 | 63.0 | 2.480                   |
| 18                 | 59.5 | 2.343                   |
| 17                 | 56.0 | 2.205                   |
| 16                 | 52.5 | 2.067                   |
| 15                 | 49.0 | 1.929                   |
| 14                 | 45.5 | 1.791                   |
| 13                 | 42.0 | 1.654                   |
| 12                 | 38.5 | 1.516                   |
| 11                 | 35.0 | 1.378                   |
| 10                 | 31.5 | 1.240                   |
| 9                  | 28.0 | 1.102                   |
| 8                  | 24.5 | 0.965                   |
| 7                  | 21.0 | 0.827                   |
| 6                  | 17.5 | 0.689                   |
| 5                  | 14.0 | 0.551                   |
| 4                  | 10.5 | 0.413                   |
| 3                  | 7.0  | 0.276                   |
| 2                  | 3.5  | 0.138                   |
| POLZAHL<br>n POLES |      | L1<br>[mm] L1<br>[inch] |

|                                                                                                                            |            |          |                                                                                                                    |                                                                          |                                                                                                          |
|----------------------------------------------------------------------------------------------------------------------------|------------|----------|--------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|
| <div></div> <div>DIN ISO 2768-m</div> |            |          |                                                                                                                    | Cat.no.: .                                                               |                                                                                                          |
| <div>93783/5<br/>24.11.17 HELIS_MA</div>                                                                                   |            | 02       | <div><b>Weidmüller</b> </div> |                                                                          | <div>3 23142 </div> |
| Modification                                                                                                               |            |          | <div>Drawing no. <span>Issue no.</span></div>                                                                      |                                                                          |                                                                                                          |
|                                                                                                                            |            |          | <div>Sheet 01 of 01 sheets</div>                                                                                   |                                                                          |                                                                                                          |
| <div></div>                           |            | Date     | Name                                                                                                               | <div><b>BLZF 3.50/.. /180..</b><br/>BUCHSENSTECKER<br/>FEMALE PLUG</div> |                                                                                                          |
| Drawn                                                                                                                      | 10.12.2007 | HELIS_MA |                                                                                                                    |                                                                          |                                                                                                          |
| Responsible                                                                                                                |            | AMANN_A  |                                                                                                                    |                                                                          |                                                                                                          |
| Checked                                                                                                                    | 08.01.2018 | HELIS_MA |                                                                                                                    |                                                                          |                                                                                                          |
| Scale: 2/1                                                                                                                 |            |          |                                                                                                                    |                                                                          |                                                                                                          |
| Supersedes: .                                                                                                              | Approved   |          | LANG_T                                                                                                             | Product file: BLZF 3.50 <span>7357</span>                                |                                                                                                          |