

## Han E Male Contact CuNi 0.14-0.37 mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6163
Specification	Han E Male Contact CuNi 0.14-0.37 mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09330006163">https://b2b.harting.com/09330006163</a>

### Identification

Category	Contacts
Series	Han E <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Male
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance  
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	25
Net weight	1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140049864
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors