






RoHs

General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

0.1/10

±2°



PCB LAYOUT

Product model	PIN	A	B	C
DA508-141C1-2PG213	2	12.16	5.08	5.08
DA508-141C1-3PG213	3	17.24	10.16	10.16
DA508-141C1-4PG213	4	22.32	15.24	15.24
DA508-141C1-5PG213	5	27.40	20.32	20.32
DA508-141C1-6PG213	6	32.48	25.40	25.40
DA508-141C1-7PG213	7	37.56	30.48	30.48
.....				
DA508-141C1-24PG213	24	5.08xN+2	5.08x(N-1)	5.08x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	/	320/20	/
Rate Impulse Voltage(KV)	/	4	/
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40°C~+105°C		
Conform to RoHS	Yes		

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES
UNLESS SPECIFIED



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.	TITLE:
DA508-141C1-NPG213	Socket-type terminal
DESIGN:	CUSTOMER
James	SIZE
CHED:	A4
Talen	UNITS
APPD:	MM
Sophia	SCALE
	N:A
	SHEET
	1/1