


Actuator

45-
2828.2C50.001



<https://eao.com/p/45-2828.2C50.001>

Your product:



45-2828.2C50.001 Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front bezel colour:	Silver
Front bezel material:	Metal

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lever colour:	Green
Lever shape:	short
Lever material:	plastic

MECHANICAL CHARACTERISTIC

Weight:	0.04 kg
Switching action:	Rest - Maintained
Switching positions:	2 positions
Switching angle:	90° right / -45° ... +45°
Mechanical lifetime:	1 Mio. cycles of operation
Operating frequency:	1 800/h


AMBIENT CONDITION

IP front protection:	IP66, IP67, IP69K
----------------------	-------------------


Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6
Vibration resistance:	According to IEC 60068-2-6: 10 ... 500 Hz: 5 g
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

OTHER


Housing material:	Metal
Hints:	External diameter of the short lever 32.3 mm
Short Description:	Actuator, Ø 29,5 mm, optional illuminative, Green, short, Silver, Metal, Rest - Maintained, IP66, IP67, IP69K
Wiring diagrams:	



Dimension drawings:



Switching positions:



Mounting cut-outs:

