






LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A1		INITIAL RELEASED	17JUN2011	AY	SZ	




- 1 PART NUMBER AND DATE CODE TO BE MARKED
- 2 MATERIAL: HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0.
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES
- 7 PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN SnPb OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 DIAMETER HOLE



SECTION Z-Z



1.375	2.050	.250	.250	.450	2.900	2.950	3.250	4P + 24S + 4P	6450660-1	
DIM W	DIM R	DIM S	DIM T	DIM K	DIM U	DIM D	DIM L	DESCRIPTION	PART NUMBER	
				THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN A. YANG 17JUN2011		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:			CHK S. ZHAO 17JUN2011		NAME RIGHT ANGLE RECEPTACLE ASSEMBLY PRESS FIT .150 THR HOLE MULTI-BEAM XL			
		0 PLC ±.01 1 PLC ±.01 2 PLC ±.005 3 PLC ±.0020 ANGLES ±2°			APVD JH. CHEN 17JUN2011					
					PRODUCT SPEC 108-1973 APPLICATION SPEC 114-13038					
MATERIAL 		FINISH 			WEIGHT -		SIZE A1	CAGE CODE 00779	DRAWING NO C6450660	
CUSTOMER DRAWING							SCALE 4:1		SHEET 1 OF 2	REV A2

[illegible]

D	SIGNAL CONTACT, PRESS-FIT, TAIL LENGTH .119	D
C	SIGNAL CONTACT, PRESS-FIT, TAIL LENGTH .119	C
B	SIGNAL CONTACT, PRESS-FIT, TAIL LENGTH .119	B
A	SIGNAL CONTACT, PRESS-FIT, TAIL LENGTH .119	A
RS	POWER CONTACT, STD, PRESS FIT, TAIL LENGTH .119	-
CODE	DESCRIPTION	ROW

4805 (3/11)