



LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
						APVD
		C1		REVISED PER ECR-10-006140	08APR10	HMR
						GJ

D




C

B

A



- 1 MAGNET WIRE: #18-#34 AWG, 1.02-0.16 [.40-.006] DIA COPPER.
- 2 POCKET RECOMMENDATION: 1601431.
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 10.
- 4 ROUNDED TAB TO FIT THROUGH 1.60 [.063] DIA RING GAGE. WILL NOT PASS THRU 1.50 [.059] DIA RING GAGE OVER INDICATED LENGTH.
- 5 TWO (2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.



PRE-TIN PLATE OVER COPPER UNDERPLATE	2-1601187-2
PRE-TIN PLATE OVER COPPER UNDERPLATE	1601187-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 06JAN2004	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK GENE JACONO 06JAN2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD GENE JACONO 06JAN2004	NAME	
0 PLC ± -		PRODUCT SPEC	PSEUDO ROUND TAB	
1 PLC ± -		APPLICATION SPEC	SIAMEZE TERMINAL	
2 PLC ± 0.13 [.005]			-	
3 PLC ± -			SIZE	
4 PLC ± -			CAGE CODE	
ANGLES ± 2°			DRAWING NO	
FINISH			RESTRICTED TO	
MATERIAL			SCALE	
BRASS, 3/4 HARD			SHEET	
SEE TABLE			REV	
			C1	