





△ GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27μm NICKEL MIN.AND ACTION
PIN: 0,5μm TIN MIN.
FOR PLATING OF MATING SURFACES SEE PERFORMANCE LEVEL
SHOWN IN PART NUMBER TABLE.

△ MATERIAL; PHOSPHORBRONZE.

△ ROW "f" 6 PLATED THROUGH HOLES FOR UPPERSHIELD
△ HOLE PATTERN FOR FEMALE CONNECTOR TYPE C
△ 55 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
△ SHIELDS LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REF: TR-NWT-001217 ISSUE 1, SEPT. 1992.


△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.

△ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.

△ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III,CENTRAL OFFICE APPLICATIONS.

△ 0.76μm MIN GOLD PLATING AT MATING SURFACE.



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

6 OBSELETE		1 2 10		2		8-5352111-4					
		1 5 9		2		5352111-9					
		1 7		2		5352111-2					
		FINISH		MATERIAL		PARTNUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.N.KIRAN 18AUG04		TE TE Connectivity							
DIMENSIONS: mm		CHK B.MOOIJ 25MAR05									
0-PLC 1-PLC 2-PLC 3-PLC 4-PLC ANGLES ± ± ± ± ± ± ±0.2		APVD B.MOOIJ 25MAR05		NAME Z-PACK 2mm HM GROUND RETURN UPPER SHIELD TYPE C/M							
		PRODUCT SPEC 108-19082									
		APPLICATION SPEC 114-19029									
		MATERIAL -		FINISH -		SIZE A2		CAGE CODE 00779		DRAWING NO C-5352111	
CUSTOMER DRAWING		WEIGHT -		SCALE 5:1		SHEET 1 of 1		REV D			