

ALL RIGHTS RESERVED.

REVISIONS

4. CUTTING BURR MAX. 1mm ALLOWED.



1776293-4 AS SHOWN

OBSOLETE	80.0	94.0±1.0	12	TSB23012DS	1-1776293-2
	72.0	86.0±0.7	11	TSB23011DS	1-1776293-1
	64.0	78.0±0.7	10	TSB23010DS	1-1776293-0
	56.0	70.0±0.7	9	TSB23009DS	1776293-9
	48.0	62.0±0.7	8	TSB23008DS	1776293-8
	40.0	54.0±0.7	7	TSB23007DS	1776293-7
	32.0	46.0±0.7	6	TSB23006DS	1776293-6
	24.0	38.0±0.5	5	TSB23005DS	1776293-5
	16.0	30.0±0.5	4	TSB23004DS	1776293-4
	8.0	22.0±0.5	3	TSB23003DS	1776293-3
	—	14.0±0.5	2	TSB23002DS	1776293-2
	—	6.0±0.3	1	TSB23001DS	1776293-1
DIM B	DIM A	NO POSN	CATALOG NUMBER	TE PART NUMBER	

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

WEIGHT

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm -$
1 PLC	± 0.3
2 PLC	± 0.25
3 PLC	$\pm -$
4 PLC	$\pm -$
ANGLES	$+ 2^\circ$

SEE NOTES

SEE NOTES

WEI

STE

TE Connectivity Ltd.

NAME	EUROPA TERMINAL BLOCK W/WIRE PROTECTOR MOUNTING HOLES 2.8 DIA., 8.0mm PITCH
------	--

RESTRICTED TO

A

00779

C-1776293

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 1

REV P1