







2

SINGLE LATCH DETAIL FOR
2324245-8 AND 1-2324245-0

2

SINGLE LATCH DETAIL FOR
1-2324245-2 THRU 1-2324245-6

●

KINKED STANDARD DIRECTION

○

NO KINK

8P

10P

12P

14P

16P

18P

20P

22P

24P

26P

28P

30P

32P

34P

36P

38P

40P

40

39

38

37

36

35

34

33

32

31

30

29

28

27

26

25

24

23

22

21

20

19

18

17

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1

POS

KINKED PIN CHART

Ø 0.90
[.035]

-X-

Ø 0.90
[.035]

⊕ 0.10 [.004] Z X-X2 Y

Ø 0.90
[.035]

-X2-

1.60
[.063]

Ø 1.20
[.047]

1.60
[.063]

2.50
[.098]

2.50
[.098] TYP

DIM F

1.50±0.10
[.059±.003]

3.50 REF
[.138]

3.50 REF
[.138]

Y

Z

RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
WARREN HUO
26AUG2018

CHK
DANIEL ZHANG
27AUG2018

APVD
DANIEL ZHANG
27AUG2018

DIMENSIONS:
mm[INCHES]

0

PLC

±

1

PLC

±

2

PLC

±0.25 [.010]

3

PLC

±

4

PLC

±

ANGLES

±

FINISH

±

MATERIAL

-

PRODUCT SPEC
108-106357

APPLICATION SPEC
114-13315

WEIGHT
-

CUSTOMER DRAWING

NAME
ASSEMBLY, PIN HEADER,
EP 2.5, DUAL ROW, GLOW WIRE
VERTICAL, WITH BOSS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2324245

RESTRICTED TO
-

SCALE
N/A

SHEET
2

OF
2

REV
A

1471-9 (3/11)