





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DNW	APV
		C		REVISED PER ECO-14-005775	21APR2014	AP	DD




- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
- 4 UNGUIDED RIGHT ANGLE MALE MATES TO UNGUIDED RIGHT ANGLE RECEPTACLE.
- 5 TE LOGO LOCATED IN APPROXIMATE LOCATION.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DNW	07APR2011	TE Connectivity
		CHG	07APR2011	
DIMENSIONS:	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		
		0 PLC	±0.25	
		1 PLC	±0.13	
		2 PLC	±0.13	
		3 PLC	±0.13	
		4 PLC	±0.13	
		ANGLES	±10°	
MATERIAL		PRODUCT SPEC		
		APPLICATION SPEC		
		CAGE CODE		
		DRAWING NO.		
		WEIGHT		
		A100779	C=2143310	
		CUSTOMER DRAWING		
		SCALE	5:1	
		SHEET	1	OF 2
		REV	C	

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DNW
AD	00	-	SEE SHEET 1	-	-	-




COPLANAR MATED SIGNAL PATHS

DC PIN A10 ----- RAM PIN A10

DC PIN A1 ----- RAM PIN A1

3	5.50	2143310-6
3	4.90	2143310-5
2	5.50	2143310-3
2	4.90	2143310-2
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
 FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DNW	07APR2011	TE Connectivity
		CHG	07APR2011	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
mm		APVD EASY 07APR2011		
		0 PLC	±0.25	
		1 PLC	±0.25	
		2 PLC	±0.13	
		3 PLC	±0.13	
		4 PLC	±0.13	
		ANGLES	±10°	
MATERIAL	PIN FINISH	SEE TABLE		
NAME		IMPACT, STD, RAM, 2 PAIR, 16 COLUMN, UNGUIDED LEFT END WALL SIGNAL MODULE, 0.39 EYELET		
PRODUCT SPEC				
APPLICATION SPEC				
SIZE		CAGE CODE		DRAWING NO.
WEIGHT		A100779		2143310
CUSTOMER DRAWING				REV C
SCALE 5:1		SHEET 2 OF 2		