

## Within Series Adaptor 46\_N-50-0-1/133\_N

### Description

T-adaptor, 3 jacks  
N jack (female) / N jack (female)

Interface standard  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 11 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0701 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00013510

### Ordering Information

Single package 46\_N-50-0-1/133\_NE