



PROJECT NR.:		REVISIONS				
PRJ-11-000004377		ÄNDERUNGEN				
P	LTR	DESCRIPTION BESCHREIBUNG		DATE	DWN	APVD
	A	NEW RELEASE		04DEC2014	TJ	PS
	A1	PN 3-2172067-2 DISCONTINUED		27OCT2017	TJ	NG



TECHNICAL DATA	2-2172067-2	3-2172067-2
RATED VOLTAGE	60V	30V
RATED IMPULSE VOLTAGE	800V	800V
POLLUTION DEGREE	3	3
OVERVOLTAGE CATEGORY	II	II
MATERIAL GROUP	II	II
RATED CURRENT	4A	4A
VOLUME RESISTIVITY	≤ 3mΩ	≤ 3mΩ
DEGREE OF PROTECTION	IP67	IP67
UPPER TEMPERATURE	+85 °C	+85 °C
LOWER TEMPERATURE	-40 °C	+40 °C






PIN ARRANGEMENT

2-2172067-2

3-2172067-2



CONDUCTOR LAYOUT



NOTES

- 1 MATERIAL: ITEM NO. 1: CONTACT BODY - PA
ITEM NO. 2: CONTACT - CuZn (BRASS)
CONTACT FINISH - Au (GOLD)
- 2 ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED

OBSOLETE	⚠	4	3-2172067-2
	⚠	3	2-2172067-2
MATERIAL	NUMBER OF POLES	TE-PART-NO.	

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		DWN YASHKUMAR 25JUL2014 CHK M. BRUBAKER 25JUL2014 APVD M. BRUBAKER 25JUL2014		NAME M8 RECEPTACLE, MALE, PCB MOUNT, ANGLED	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		PRODUCT SPEC 108-19483 APPLICATION SPEC 114-32127		SIZE A2 CAGE CODE 00779 DRAWING NO. C-2172067	
DIMENSIONS: MASSEINHEITEN: IT(M)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		RESTRICTED TO NUR FÜR -	
MATERIAL		SEE NOTES		SHEET 1 OF 1	
SEE NOTES		SEE NOTES		REV A1	

SIZE ISO 14405 Ⓢ