



UF2002FCT SERIES

ULTRAFAST RECOVERY RECTIFIERS

VOLTAGE 200 to 600 Volt **CURRENT** 20 Ampere

ITO-220AB


Unit : inch(mm)

FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-O utilizing Flame Retardant Epoxy Molding Compound.
- Low power loss, high efficiency.
- Low forward voltage, high current capability
- High surge capacity.
- Ultra fast recovery times, high voltage.
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case: ITO-220AB full molded plastic package
- Terminals: Lead solderable per MIL-STD-750, Method 2026
- Polarity: As marked.
- Standard packaging: Any
- Weight: 0.056 ounces, 1.6 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

PARAMETER	SYMBOL	UF2002FCT	UF2003FCT	UF2004FCT	UF2006FCT	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	200	300	400	600	V
Maximum RMS Voltage	V_{RMS}	140	210	280	420	V
Maximum DC Blocking Voltage	V_{DC}	200	300	400	600	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$	20				A
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	150				A
Maximum Forward Voltage at 10A	V_F	1	1.3		1.7	V
Maximum DC Reverse Current at Rated DC Blocking Voltage	I_R	1 250				μA
Typical Junction Capacitance (Notes 1)	C_J	200				pF
Maximum Reverse Recovery Time (Notes 2)	t_{rr}	50			100	ns
Typical Thermal Resistance (Notes 3)	$R_{\theta JC}$	7				°C / W
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 to +150				°C

NOTES :

1. Measured at 1 MHz and applied reverse voltage of 4 VDC.
2. Reverse recovery test conditions: $I_F=0.5A$, $I_R=-1A$, $I_{rr}=-0.25A$.
3. Thermal resistance from junction to ambient and from junction to lead



UF2002FCT SERIES




Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 UF2002FCT Typical Reverse Characteristics




Fig.4 UF2003FCT & UF2004FCT Typical Reverse Characteristics




Fig.5 UF2006FCT Typical Reverse Characteristics




Fig.6 UF2002FCT Typical Forward Characteristics




Fig.7 UF2003FCT & UF2004FCT Typical Forward Characteristics




Fig.8 UF2006FCT Typical Forward Characteristics



UF2002FCT SERIES


Part No_packing code_Version

UF2002FCT_T0_00001

For example :

RB500V-40_R2_00001

Part No.



Packing Code XX				Version Code XXXXX		
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number
Bulk Packing (B/P)	B	13"	2			
Tube Packing (T/P)	T	26mm	X			
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y			
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U			
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D			



UF2002FCT SERIES

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.