






620-006

Split Strain Reliefs

Rotatable Coupling - Straight and 90°

CONNECTOR DESIGNATOR **A-F-H-L** ROTATABLE COUPLING



620-006
Split Strain Reliefs
Rotatable Coupling - Straight and 90°



62

TABLE III: CABLE ENTRY

Shell Size Conn. Desig.		E		F		G		H Cable Entry				J		K	
A,F,L	H	Max		Nom		Min		Closed		Open		Max		Max	
08	09	.602	(15.3)	.752	(19.1)	.125	(3.2)	.125	(3.2)	.204	(5.2)	.808	(20.3)	.704	(17.9)
10	11	.712	(18.1)	.832	(21.1)	.125	(3.2)	.187	(4.7)	.286	(7.3)	.867	(22.0)	.786	(20.0)
12	13	.837	(21.3)	.988	(25.1)	.188	(4.8)	.291	(7.4)	.416	(10.6)	.929	(23.6)	.979	(24.9)
14	15	.837	(21.3)	1.046	(26.6)	.188	(4.8)	.351	(8.9)	.476	(12.1)	.992	(25.2)	1.039	(26.4)
16	17	.962	(24.4)	1.319	(33.5)	.188	(4.8)	.501	(12.7)	.625	(15.9)	1.056	(26.8)	1.188	(30.2)
18	19	1.212	(30.8)	1.451	(36.9)	.250	(6.4)	.578	(14.7)	.706	(17.9)	1.233	(31.3)	1.300	(33.0)
20	21	1.337	(34.0)	1.557	(39.5)	.250	(6.4)	.581	(14.8)	.831	(21.1)	1.296	(32.9)	1.425	(36.2)
22	23	1.462	(37.1)	1.653	(42.0)	.312	(7.9)	.644	(16.4)	.956	(24.3)	1.358	(34.5)	1.550	(39.4)
24	25	1.587	(40.3)	1.775	(45.1)	.312	(7.9)	.706	(17.9)	1.081	(27.5)	1.420	(36.1)	1.675	(42.5)
28		1.731	(44.0)	2.020	(51.3)	.312	(7.9)	.750	(19.1)	1.187	(30.1)	1.634	(41.5)	1.813	(46.1)

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.