


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D	REVISED ECO-05-007228	30AUG2005	SW	CR
			DI	ADDED 1--5, ECO-05-010011	09NOV2005	SW	CR
			E	REVISED ECO-06-022418	26SEP2006	SW	CR
			F	REVISED PER ECO-08-003247	06FEB2008	SS	CR

D


C

B


A




- 1 MATERIAL AND FINISH
HOUSING: PA 6.6, UL 94 V-0 RATED, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: BRASS, NICKEL PLATED.
2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
3. WIRE RANGE: 14-30 AWG.
- 4 NOT CUMULATIVE TOLERANCE.
5. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.
- 6 MARKED WITH PERMANENT WHITE INK IN APPROX AREA SHOWN.



DETAIL Z



1546173-3 AS SHOWN

PRELIMINARY	SEE DETAIL Z	4	ALL	20.0	4	1-1546173-5
	-	5	1, 3, 5, 7, 8	40.0	8	1-1546173-4
	-	12	ALL	60.0	12	1-1546173-2
	-	11	ALL	55.0	11	1-1546173-1
	-	10	ALL	50.0	10	1-1546173-0
	-	9	ALL	45.0	9	1546173-9
	-	8	ALL	40.0	8	1546173-8
	-	7	ALL	35.0	7	1546173-7
	-	6	ALL	30.0	6	1546173-6
	-	5	ALL	25.0	5	1546173-5
	-	4	ALL	20.0	4	1546173-4
	-	3	ALL	15.0	3	1546173-3
-	2	ALL	10.0	2	1546173-2	
SPECIAL MARKING	QTY	SELECTIVELY LOADED IN POSTIONS		L	NO OF POSN	PART NUMBER
	CONTACTS					
THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.0000 ANGLES ± FINISH		DWN S. WELDON CHK D. BIEVENOUR APVD D. BIEVENOUR	18APR2002 18APR2002 18APR2002	
				PRODUCT SPEC -		NAME TERMINAL BLOCK, PLUG, 90 DEGREE, STACKING, 5.0mm PITCH
				APPLICATION SPEC -		
				WEIGHT -		
MATERIAL 				A200779		C=1546173
CUSTOMER DRAWING				SCALE	4:1	SHEET 1 OF 1
						REV F

D

C

B

A