



TYPE 1
类型 1


Single PG/M thread
单个 PG/M螺纹孔




PG/M THREAD-1
PG/M 螺纹1



2X M6 SCREW
2X M6 螺丝




4X M3 THREAD
4X M3 螺纹孔



TYPE 2
类型 2

Two PG/M threads
两个 PG/M螺纹孔




PG/M THREAD-2
PG/M 螺纹2

PG/M THREAD-3
PG/M 螺纹3

All dimension is same as TYPE 1,except those defined in this TYPE
除了在本类型中定义的尺寸外,其他尺寸同类型 1

TYPE 3
类型 3

Three PG/M threads
三个 PG/M螺纹孔



PG/M THREAD-1
PG/M 螺纹1



PG/M THREAD-2
PG/M 螺纹2

All dimension is same as TYPE 1,except those defined in this TYPE
除了在本类型中定义的尺寸外,其他尺寸同类型 1

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	07JUN2016	DW	CW
	A1	ECR-17-018159	13DEC2017	RL	CW
	A2	ECR-18-012258	01AUG2018	DW	CW
	B	ECR-20-016312	03JUN2021	BS	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 07JUN2016	 TE Connectivity	
DIMENSIONS: mm		CHK CHRIS WANG 07JUN2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XIANG XU 07JUN2016	NAME H24BPR-TGHC-PG/M-EMC-C	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-137191	SIZE A1	
MATERIAL -		APPLICATION SPEC 114-137191	CAGE CODE -	
FINISH -		WEIGHT -	DRAWING NO C=T192224XXXXX09	
CUSTOMER DRAWING		SCALE 1:1	SHEET 1	REV B

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:
SEE SHEET 1

T1922240320-009	H24BPR-TGHC-3M20-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY 3M20,BLACK H24BPR上壳,中部锁定,顶出3M20,黑色	M20	M20	M20	TYPE 3 类型3
T1922241221-009	H24BPR-TGHC-2PG21-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY 2PG21,SILVER WHITE H24BPR上壳,中部锁定,顶出2PG21,银白色	PG21	PG21	-	TYPE 2 类型2
T1922242150-009	H24BPR-TGHC- M50-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M50,GREY H24BPR上壳,中部锁定,顶出M50,灰色	-	-	M50	
T1922241140-009	H24BPR-TGHC-M40-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M40,SILVER WHITE H24BPR上壳,中部锁定,顶出M40,银白色	-	-	M40	
T1922241136-009	H24BPR-TGHC-PG36-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG36,SILVER WHITE H24BPR上壳,中部锁定,顶出PG36,银白色	-	-	PG36	
T1922241132-009	H24BPR-TGHC-M32-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M32,SILVER WHITE H24BPR上壳,中部锁定,顶出M32,银白色	-	-	M32	
T1922241129-009	H24BPR-TGHC-PG29-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG29,SILVER WHITE H24BPR上壳,中部锁定,顶出PG29,银白色	-	-	PG29	
T1922241125-009	H24BPR-TGHC-M25-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M25,SILVER WHITE H24BPR上壳,中部锁定,顶出M25,银白色	-	-	M25	
T1922241121-009	H24BPR-TGHC-PG21-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG21,SILVER WHITE H24BPR上壳,中部锁定,顶出PG21,银白色	-	-	PG21	
T1922240140-009	H24BPR-TGHC-M40-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M40,BLACK H24BPR上壳,中部锁定,顶出M40,黑色	-	-	M40	
T1922240136-009	H24BPR-TGHC-PG36-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG36,BLACK H24BPR上壳,中部锁定,顶出PG36,黑色	-	-	PG36	
T1922240132-009	H24BPR-TGHC-M32-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M32,BLACK H24BPR上壳,中部锁定,顶出PG32,黑色	-	-	M32	
T1922240129-009	H24BPR-TGHC-PG29-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG29,BLACK H24BPR上壳,中部锁定,顶出PG29,黑色	-	-	PG29	TYPE 1 类型1
T1922240125-009	H24BPR-TGHC-M25-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY M25,BLACK H24BPR上壳,中部锁定,顶出M25,黑色	-	-	M25	
T1922240121-009	H24BPR-TGHC-PG21-EMC-C	H24BPR HOOD,CENTER LOCKING, TOP ENTRY PG21,BLACK H24BPR上壳,中部锁定,顶出PG21,黑色	-	-	PG21	
PART NUMBER 料号	DESCRIPTION 描述		PG/M THREAD-3 PG/M 螺纹3	PG/M THREAD-2 PG/M 螺纹2	PG/M THREAD-1 PG/M 螺纹1	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.
TOLERANCES UNLESS OTHERWISE SPECIFIED:

DIMENSIONS:
mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

±

±

±

±

±

ANGLES

FINISH

±

-

DWN
DAVID WANG
CHK
CHRIS WANG

07JUN2016

07JUN2016

APVD
XIANG XU

07JUN2016

PRODUCT SPEC

108-137191

APPLICATION SPEC

114-137191

WEIGHT

-

CUSTOMER DRAWING

NAME

H24BPR-TGHC-PG/M-EMC-C

SIZE

A1

CAGE CODE

-

DRAWING NO

©=T192224XXXXX09

RESTRICTED TO

SCALE

1:1

SHEET

2

OF

2

REV

B

TE Connectivity