


Additional coding
View in direction B




S11YBR-P16XCD0-0000

```


Mechanical coding: B
Color coding:      red

```





S11YCR-P16XCD0-0000

Mechanical coding: C
Color coding: blue



S11YDR-P16XCDO-0000

Mechanical coding: D
Color coding: green



Delivery condition
2:1

Technical information

- Max. cable Ø6.5mm (Based on cable with one braided shield)
- Solder contacts: AWG26
- Current load: 5A@Δ+40° (Single contact)
2.5A@Δ+40° (Insert)
- Test voltage: 900V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 300V (acc. SAE AS 13441:1998) 2)

- For more technical information and accessories see catalogue (www.odu.de/amc)

- 1) For crimp information, torque, etc. see assembly instruction 010.645.001.000.002 (www.odu.de/amc/assembly)

- 2) Maximal operating voltage at sea level up to 2.000m.
Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

All shown connectors are according
to DIN EN 61984:2009
connectors without breaking capacity (COC)!

				Dimensions without tolerances acc. to middle DIN ISO 2768				PE-modell-nr.:		
								CAD-nr.:	00050988	
				2011	date	name	designation:			scale:
				prep.	09.11.	M. Meier	Push-Pull Plug AMC Standard Version			4 : 1
				app.						
				norm.						
				 otto dunkel gmbh			drawing nr.:			copy
							S11Y.R-P16XCDO-0000			
index	notice	date	name				replacement for:			nr.