


Technical drawing of a mechanical part, showing a cross-section (left) and a side view (right) with dimensions.

Dimensions:

- Overall length: 14.6 ± 0.1
- Overall diameter: $\phi 10^{+0.1}_{-0.0}$
- Inner hole diameter: $\phi 5^{+0.1}_{-0.0}$
- Threaded section length: $5.6^{+0.1}$ (B)
- Threaded section diameter: $\phi 4 \pm 0.05$ (C)
- Threaded section pitch: $0.7^{+0.1}$
- Threaded section lead-in: (2.4)
- Threaded section lead-in: (1.2)
- Threaded section lead-in: (3.6)
- Threaded section lead-in: (4.6)
- Threaded section lead-in: 60°

DIM. WITHOUT TOLERANCES				SUPERSEDES			MATERIAL BRASS			SURFACE TREATMENT BRIGHT NICKEL PLATING		
ACCORDING TO IS: 2102-m(1993)				SUPERSEDED BY								
ALL DIMENSIONS ARE IN mm.				1996	DATE	NAME	TITLE ACTUATOR PIN Ø10			FILE NAME AHP101		
				Drawn	20.12.96	Vijeth						
				Checked	15.03.00	Mahesh	DRG. No. 1 101 0009					
				Approved								
⊙	No. 147	15.3.2K		 SCALE 3:1			PAGE: 1		REV. NO.			
⊕	No. 146	15.3.2K					OFF: 1					
⊖	No. 145	15.3.2K										
No.	ALTERATION	DATE	NAME									